



Smart Plug

Make any wall socket smart with the WiZ smart plug, which includes a power meter to measure how much power the socket uses. Control your plug with the WiZ app or your voice: turn your favourite traditional lamp on and off with a tap, for example

PRODUCT HIGHLIGHTS

- Plug and Play
- With Powermeter
- Control with app or voice



Instant setup for all your smart home functionalities

Start using all your smart home features easily, by connecting your new WiZ device to your Wi-Fi network. Control your lights and devices even while you're away from home and set schedules to turn them on and off automatically. No need to install additional hardware such as hub or gateway!




Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



Make everyday devices smart: lamps, fans and more

Control regular lamps, decorative lights, fans, your coffee machine and more. Use WiZ to control devices that only need their power to be on, to link and react to the app.



Easy scheduling and automation of smart lights and devices

Schedule your home lights or appliances to turn on or off automatically and follow your daily or weekly routines. Automate your lights and devices to stay off when they're not necessary, to stay safe and save energy.



Activate devices with motion without using a sensor

WiZ's SpaceSense technology transforms your devices into motion sensors. Activate the SpaceSense feature in the WiZ app and have lights and devices turn on and off automatically, with motion detection. A minimum of two WiZ devices in a room is needed for the SpaceSense feature to work.



Built-in power metre that monitors energy consumption

This smart plug has a built-in power metre, which monitors the energy consumption of a device plugged into it. Learn how much energy your device uses by looking at the visual summary in the WiZ app.



SPECIFICATIONS

DESIGN AND FINISHING

Colour: White
Material: Plastic

EXTRA FEATURE/ACCESSORY INCL.

Plug type: Type G

INTERACTIVITY

Current (A): 13

POWER CONSUMPTION

Voltage: 240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.088 kg
Overall height: 58 mm
Overall length: 55 mm
Overall width: 55 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

IP code: IP20 | Finger-protected
Class of protection: Class I – Earthed

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514552982
Net weight: 0.09 kg
Gross weight: 0.21 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.