



Up and Down Wall Spotlight

Have fun with light patterns on your walls and create an ambience with colour. Our Up and Down Wall Light for Indoor illuminates up and down, producing interesting shapes of light, shadow, and colour, and giving character to your room.

PRODUCT HIGHLIGHTS

- Full colour
- Dimensions: 15 cm (Height) * 9.2 cm (Length) * 6.8 cm (Width)
- IP20/Metal/White



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter-certified, allowing easy control through Google Home, Amazon Alexa, Apple Home or any other Matter-based smart home platform of your choice.



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Rectangle
Dimmable: Yes

DESIGN AND FINISHING

Colour: White
Material: Metal

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: No
LED lamp(s) included: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour rendering index (CRI): ≥ 90
Colour temperature: 2200-6500 K
Warm-up time to 60% light: 2
Luminous efficacy (rated) (nom.): 69 lm/W

MISCELLANEOUS

Especially designed for: Living Room
Dining Room

OTHER CHARACTERISTICS

Lamp current: 60 mA

POWER CONSUMPTION

Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.64 kg
Overall height: 150 mm
Overall length: 92 mm
Overall width: 68 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lumen output bulb included: 345
Total lumen output fixture: 690
Light colour: 2200-6500 (RGB)
Energy class included light source: F
Wattage bulb included: 4.7
Maximum wattage replacement bulb: 5
IP code: IP20 | Finger-protected
Class of protection: Class I – Earthed
Light source replaceable: Yes
Number of light sources: 2

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514554597
Net weight: 0.64 kg
Gross weight: 0.69 kg
Height: 16.1 cm
Length: 10.5 cm
Width: 7.8 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.