




Bulb 60W A60 B22



The WiZ LED A60 full-colour bulb brings smart lighting for your daily living. Retrofit into any lamp shade to create the ambience of your choice with 16 million colours, as well as warm to cool white light. You can set a schedule to turn lights on and off according to daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

PRODUCT HIGHLIGHTS

- Full colour smart bulb
- Up to 806 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!

Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.

Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.

Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: A60
Socket: B22
Type of glass: Frosted
Dimmable: Yes

LAMP DIMENSIONS

Weight: 0.065 kg

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): ≥80
Colour temperature: 2200-6500 K
Light Colour Category: Full colour
Nominal luminous flux: 806 lm
Starting time: <0.5 s
Warm-up time to 60% light: Instant full light
Luminous efficacy (rated) (nom.): 94 lm/W

OTHER CHARACTERISTICS

Lamp current: 65 mA

PACKAGING INFORMATION

EAN: 8720169072312
EOC: 872016907231200
Product title: Wi-Fi BLE 60W A60 B22 822-65 RGB 1PF/6

POWER CONSUMPTION

Power factor: 0.5
Voltage: 220-240 V
Wattage equivalent: 60 W
Energy efficiency label (EEL): F
Power Consumption: 8.5 W
Energy consumption kWh/1,000 hours: 9

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 120 mm
Overall length: 120 mm
Overall width: 60 mm

RATED VALUES

Rated lifetime: 25,000
Rated luminous flux: 806 lm
Rated power: 8.5 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60
EPREL Registration Number: 1421110
Flux measurement reference: Sphere

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169072312
Net weight: 0.05 kg
Gross weight: 0.09 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.