



Superslim Ceiling 32W

Super slim is super with sleek WiZ ceiling lights. Dynamic full-colour light modes bring on the joy, whether you're partying or spending some down time with your significant others. Or dial up the perfect shade of white light: cool daylight for concentration and productivity, cosy candlelight for chilling or anything in between. The minimalist black housing smartly accents your décor. Enjoy all the energy-saving benefits of LED with no glare, no flickering and no eye strain, Wi-Fi controllable, of course, using the WiZ app, WiZ remote or your voice.

PRODUCT HIGHLIGHTS

- Full colour
- Dimensions: Ø545
- IP20/Plastic/Black



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Create your perfect light scene

Make your own mix of different colour and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colours and changing light modes to make your day

Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Round
Dimmable: Yes

DESIGN AND FINISHING

Colour: Black
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 20 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 15,000
Nominal lifetime: 20,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Colour consistency: 6 SDCM
Colour rendering index (CRI): ≥80
Colour temperature: 2200-6500 K
Warm-up time to 60% light: 2
Luminous efficacy (rated) (nom.): 117
lm/W

MISCELLANEOUS

Especially designed for: Living Room
Dining Room Bedroom Children's
room

OTHER CHARACTERISTICS

Lamp current: 160 mA

POWER CONSUMPTION

Power factor: 0.9
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 2.4 kg
Overall height: 38 mm
Overall length: 545 mm
Overall width: 545 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 545 mm
Total lumen output fixture: 3750
Light colour: 2200-6500 (RGB)
Wattage bulb included: 32
IP code: IP20 | Finger-protected
Class of protection: Class II – Double
Insulated

WHAT'S SUPPORTED

Compatible with Effects feature: Yes
WiFi: Wireless G
Defined support period: Minimum of
60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8720169072671
Net weight: 2.2 kg
Gross weight: 2.61 kg
Height: 55 cm
Length: 3.9 cm
Width: 54.5 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.