

# PHILIPS

Globe 11W  
(Eq.75W) G95 E27

Smart LED

Full colour

Plastic

Easy plug and play

Control with app or voice



8720169170919



## Smart lighting for your daily living

Bring human-centric lighting into your life with this smart WiZ LED globe-shape bulb. Apply different shades of warm to cool white to help you focus or relax. You can set a schedule to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

### Easy setup

- Smart lighting functionalities easy to set up

### Smart control

- Control from anywhere with your smartphone.

### Smart features

- Preset wellbeing features
- Set up lights to follow your own schedule

### Light modes

- Customise Scenes with preset dynamic light modes.

# Highlights

## Instant set-up



Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!

### Control from anywhere

Control your devices wherever you are with smartphone. No need to worry if you've left your devices on before leaving home. WiZ app is available for iOS and Android.

## Preset wellbeing features



Use the preset wellbeing features in the WiZ app to and enjoy the lighting pattern best suited for your circadian rhythm through the day. WiZ will provides you bright daylight when you need to get energised and focus, and transition smoothly to soft warm white to help you relax and sleep better.

## Light automation schedule



Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.

### Customised Scenes

Mix different colour and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out at any time with app, WiZmote or voice.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: G95
- Socket: E27
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: Yes

## Lamp dimensions

- Weight: 0.11 kg

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your colour: Yes
- Fully weatherproof: No
- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

### Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI):  $\geq 80$
- Colour temperature: 2700/6500
- Light Colour Category: Full colour
- Nominal luminous flux: 1055 lm
- Starting time:  $< 0.5$  s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 95

### Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room, Children's room
- EyeComfort: Yes

### Other characteristics

- Lamp current: 75 mA

### Packaging information

- EAN: 8720169170919
- EOC: 872016917091900
- Product title: PHI WFB 75W G95 E27 822-65 RGB 1PF/6

### Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 75 W
- Energy efficiency label (EEL): F
- Power: 11 W
- Energy consumption kWh/1,000 hours: 11

### Product dimensions and weight

- Overall height: 139 mm
- Overall length: 139 mm
- Overall width: 95 mm

### Rated values

- Rated lifetime: 25,000
- Rated luminous flux: 1055 lm
- Rated power: 11 W

### Technical specifications

- Frequency: 50–60
- Diameter: 95 mm
- Bulb technology: LED
- IP code: IP20 | Finger-protected
- EPREL Registration Number: 1421113
- Flux measurement reference: Sphere

### The bulb

- Diameter: 95 mm
- Software upgradable: Yes

### What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

### Packaging dimensions and weight

- EAN/UPC - product: 8720169170919
- Net weight: 0.1 kg
- Gross weight: 0.21 kg
- Height: 18.5 cm
- Length: 10.5 cm
- Width: 10.5 cm



Issue date: 2026-04-29  
Version: 0.297

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)