

PHILIPS

Bulb 8.5W (Eq.60W)
A60 E27 x2

Smart LED

Full colour

Plastic

Easy plug and play

Control with app or voice



8720169171060



Smart lighting for your daily living

Enjoy more convenience in everyday life with this smart WiZ LED A60 bulb. This bulb gives soft white light that dims to your desired brightness level via app or voice. You can set schedule to turn lights on and off according to your daily or weekly routines, and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

Smart control

- Connected by WiZ

Smart features

- SpaceSense motion detection

Smart devices

- Matter-certified

Light modes

- Millions of colours
- Tunable white light
- Low dimming

Highlights

Connected by WiZ

Fully compatible with all Connected by WiZ products – use the WiZ app to set up and unlock all the benefits of smart lighting.

SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WiZ lights or devices.

Matter-certified



Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

Millions of colours

Choose any light colour from the palette or apply a preset light mode, like Fireplace or Ocean, to create an amazing atmosphere and set the mood.

Tunable white light

Easily adjust from cool, bluish hues that enhance visibility and focus to soft, warmer tones for relaxing in the evening (CCT range 2,200 K–6,500 K).

Low dimming

Dim your light smoothly from full brightness down to 1% to achieve the right level of light for whatever you're doing.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: E27
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: Yes

Lamp dimensions

- Weight: 0.05 kg

Design and finishing

- Colour: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your colour: Yes
- Fully weatherproof: No
- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700/6500
- Light Colour Category: Full colour
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 94

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room, Children's room
- EyeComfort: Yes

Other characteristics

- Lamp current: 65 mA

Packaging information

- EAN: 8720169171060
- EOC: 872016917106000
- Product title: PHI WFB 60W A60 E27 822-65 RGB 2PF/6

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): F
- Power: 8.5 W
- Energy consumption kWh/1,000 hours: 9

Product dimensions and weight

- Overall height: 11.1 mm
- Overall length: 11.1 mm
- Overall width: 6 mm

Rated values

- Rated lifetime: 25,000
- Rated luminous flux: 806 lm
- Rated power: 8.5 W

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50-60
- Diameter: 60 mm
- Bulb technology: LED
- IP code: IP20
- EPREL Registration Number: 2546660
- Flux measurement reference: Sphere

The bulb

- Diameter: 60 mm
- Software upgradable: Yes

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 8720169171060
- Net weight: 0.1 kg
- Gross weight: 0.2 kg
- Height: 16 cm
- Length: 7 cm
- Width: 14 cm



Issue date: 2026-06-17
Version: 0.418

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com