

PHILIPS

Bliss Fan Ceiling Light 35+28 W

Fan Ceiling Lights

2700/5500/4000 K

Gold

Remote Control



8720169279124



One fixture. Your switch. Three light settings.

Combine customisable light with a comfortable breeze with the Philips LED retractable ceiling fan light, which includes a remote control. With transparent blades that retract out of sight when not in use and three SceneSwitch light settings, this light creates the perfect atmosphere in any space.

Easy to experience

- Retractable ceiling fan with transparent blades
- Easy to install, safe to use
- Powerful, reliable performance
- Get year-round use
- Enjoy a comfortable breeze
- Convenient timers

Ambient light effect

- Bright yet comfortable ceiling light

Premium quality

- Quiet motor

Highlights

Retractable ceiling fan with transparent blades

Say goodbye to spinning shadows on the ceiling: this fan has transparent blades that can be folded into the light and out of sight when not in use.

Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

Powerful, reliable performance

The Philips LED ceiling fan light is designed to ensure powerful air circulation and continued reliability over time. Its wide blade design allows a large coverage of air volume to ensure maximum airflow for cooling.

Get year-round use

With operation modes for both summer and winter, you'll get the best settings to circulate the air in your space all year round.

Enjoy a comfortable breeze

Bring an island breeze to any room of your house with the Natural Breeze function, which offers dynamic speed settings for the fan.

Convenient timers

Choose from two different timers that turn off your light after a certain amount of time – and set them with the remote control.

Bright yet comfortable ceiling light

The Philips LED ceiling fan light offers powerfully bright – yet comfortable – light for your home, which you can control with the included remote control or a wall switch.

Quiet motor

The Philips LED ceiling fan light offers a quiet motor, circulating the air in the room without loud noise.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Gold
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- Extra Features: Remote control

Other characteristics

- Lamp current: 290 mA
- Efficacy: 128 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 5.8 kg
- Height: 42 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 510 mm
- Total lumen output fixture: 4500
- Light colour: 2700/5500/4000
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC – product: 8720169279124
- Net weight: 5.8 kg
- Gross weight: 7.91 kg
- Height: 28.5 cm
- Length: 54.8 cm
- Width: 54.8 cm



Issue date: 2025-05-22
Version: 0.249

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com