

PHILIPS

Purex Pedestal/ Pathway Light 1.5W

Outdoor luminaires

2700K

Black

Low Voltage; Water Resistant



8720169279599



A garden light that you can simply plug in, connect and enjoy

The Philips GardenLink low-voltage family offers a range of outdoor luminaires that you can easily and safely install. You can connect multiple lights to a single power supply and plug it into a standard socket, then easily add additional lights or reposition them whenever you like. Wiring is simple, and the low-voltage means that there's no danger of harm to you, your kids or your pets.

Ease of use

- Compatible with all GardenLink luminaires and accessories
- Easy to install with Twist & Lock connectors

Safe to use

- Extra safety with 24 V low voltage

Sustainable light solutions

- Long lifetime up to 20,000 hours

High-quality light

- Warm white light 2,700 K

Highlights

Compatible with all GardenLink luminaires and accessories

Every GardenLink luminaire offers the same Twist & Lock connector for easy installation and connection. You can reposition the luminaires and accessories as your outdoor illumination needs change, adding light to every corner of your garden.


Easy to install with Twist & Lock connectors

Super-easy installation and connection with the products' Twist & Lock connectors. Simply plug the lights in and enjoy!

Extra safety with 24 V low voltage


Low-voltage (24 V) lights are safe to install without risk of electric shock – no professional electrician required.

Long lifetime up to 20,000 hours



Reliable high-quality LED light lasts up to 20,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

Warm white light 2,700 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces warm, relaxing light at 2,700 K.

Specifications

Design and finishing

- Colour: Black
- Material: Plastic

Durability

- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

Garden area

- Garden area: Garden and Patio

Light characteristics

- Beam angle: 325 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Pedestal/Pathway Lights
- Extra Features: Low Voltage, Water Resistant

Product dimensions and weight

- Net weight: 1.45 kg
- Overall height: 530 mm
- Overall length: 60 mm
- Overall width: 60 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 180lm
- Light colour: 2700K
- Mains power: 220–240 V
- Fixture dimmable: No
- Energy class included light source: E
- Maximum wattage replacement bulb: 1.5
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: Yes

Packaging dimensions and weight

- EAN/UPC – product: 8720169279599
- Net weight: 1.45 kg
- Gross weight: 1.87 kg
- Height: 54.7 cm
- Length: 14.2 cm
- Width: 19.7 cm



Issue date: 2025-11-01
Version: 0.128

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com