

PHILIPS

Bulb 60W A60 E27
x2

Smart LED

Tunable white smart bulb

Up to 806 lumens

Easy plug and play

Control with app or voice



8720169303034

A
↑
G F



Smart lighting for your daily living

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: A60
- Socket: E27
- Type of glass: Frosted
- Dimmable: Yes
- Lamp Finish: Frosted

Lamp dimensions

- Weight: 0.05 kg

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): ≥80
- Colour temperature: 2700–6500 K
- Light Colour Category: Tunable white
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 100 lm/W

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 65 mA

Packaging information

- EAN: 8720169303034
- EOC: 872016930303400
- Product title: PHI WFB 60W A60 E27 827-65 TW 2PF/6

Power consumption

- Power factor: 0.5
- Voltage: AC 220–240 V
- Energy efficiency label (EEL): F
- Power: 8 W
- Energy consumption kWh/1,000 hours: 8

Product dimensions and weight

- Overall height: 111 mm
- Overall length: 111 mm
- Overall width: 60 mm

Rated values

- Rated lifetime: 25,000
- Rated luminous flux: 806 lm
- Rated power: 8 W

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 1877820
- Flux measurement reference: Sphere

What's supported

- Compatible with Effects feature: Yes
- WiFi: Wireless G
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, IFTTT, Klikaanklikuit, Matter, Samsung SmartThings, Sonos

Packaging dimensions and weight

- EAN/UPC – product: 8720169303034
- Net weight: 0.1 kg
- Gross weight: 0.2 kg
- Height: 16 cm
- Length: 7 cm
- Width: 14 cm



Issue date: 2026-01-31
Version: 0.179

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com