

PHILIPS

Filament Bulb Amber
50 W ST64 E27

LED

2200-2700K

640 lm

15000 h

Dimming



8720169323452



Designed to be seen

The new Deco collection transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience.

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: Yes
- Lamp Finish: Amber
- Bulb material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 330 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2200–2700 K
- Nominal luminous flux: 640 lm
- Luminous efficacy (rated) (nom.): 91 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Packaging information

- EAN: 8720169323452
- EOC: 872016932345200
- Product title: LED 50W ST64 E27 AMBER WGD SP

Power consumption

- Power factor: 0.7
- Voltage: AC 230 V
- Wattage equivalent: 50 W
- Energy efficiency label (EEL): F
- Power Consumption: 7 W
- Energy consumption kWh/1,000 hours: 7

Product dimensions and weight

- Overall height: 140 mm
- Overall length: 140 mm
- Overall width: 64 mm

Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 1902861
- Can it be used in closed luminaires: No

Packaging dimensions and weight

- EAN/UPC – product: 8720169323452
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 17.7 cm
- Length: 7 cm
- Width: 7.5 cm



Issue date: 2025-11-12
Version: 0.177

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com