

# PHILIPS

Filament Candle  
Clear 15 W T20 E14

LED

2700K

135 lm

15000 h



8720169336650



## State-of-the-art LED for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

**Choose a simple replacement for your old lamps**

- Similar shape and size as incandescent candles

# Highlights

## Similar shape and size as incandescent candles

With its beautifully shaped design and familiar dimensions, this is a

contemporary lighting, energy-saving, standard LED candle. The perfect sustainable replacement for traditional incandescent candles.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: T20
- Socket: E14
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 135 lm
- Luminous efficacy (rated) (nom.): 90 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Packaging information

- EAN: 8720169336650
- EOC: 872016933665000
- Product title: LED classic 15W T20 E14 WW CL ND SRT6

## Power consumption

- Power factor: 0.4
- Voltage: AC 220–240 V
- Wattage equivalent: 15 W
- Energy efficiency label (EEL): F
- Power Consumption: 1.5 W
- Energy consumption kWh/1,000 hours: 2

## Product dimensions and weight

- Overall height: 56 mm
- Overall length: 56 mm
- Overall width: 20 mm

## Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 1945452
- Can it be used in closed luminaires: No

## Packaging dimensions and weight

- EAN/UPC – product: 8720169336650
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 12.8 cm
- Length: 2.6 cm
- Width: 6.4 cm



Issue date: 2025-11-12  
Version: 0.286

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)