

PHILIPS


Lysin Wall Lights
EU,

Ultra-efficient Solar

4000K

Black

Dusk to
Dawn; Sensor; Solar; Water
Resistant



8720169361881



Truly long-lasting with replaceable lamp and batteries

Philips Lysin is a reliable solar light that lasts longer, reduces energy consumption and supports sustainability; it's truly long-lasting with replaceable lamp and batteries. Protected by PowerShield coating, your outdoor lights can have long-lasting beauty.

Sustainable light solutions

- Ultra-efficient solar

Bring design into your garden

- Stylish contemporary designs for your garden

Premium quality

- Durable design with PowerShield coating

Designed for outdoors

- IP44 – weatherproof

Special characteristics

- Motion and dusk-to-dawn sensor integrated

8720169361881

High-quality light

- Cool white light 4,000 K

Highlights

Ultra-efficient solar



With the Philips Ultra Efficient Solar system, these luminaires provide light for up to 35 hours on a fully-charged battery. Enjoy bright light all night, or even in bad or overcast weather conditions.

Stylish contemporary designs for your garden

These contemporary designs by Philips are stylish but understated, beautiful by day or night without overwhelming your garden or terrace. There is a full range of lights to choose from, so there is bound to be one to match your outside space and taste.

Durable design



Protected by PowerShield To keep your outdoor lights in excellent condition, we use a high-performance powder coating powered by Interpon, an AkzoNobel brand. Tougher than traditional paints, it protects against fading, scratches, dents and rust for long-lasting beauty and performance.

IP44 – weatherproof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water – perfect for general outdoor use.

Motion and dusk-to-dawn sensor integrated



With a built-in motion sensor, these lights automatically welcome you when you return home after dark, or light up when visitors arrive. The unique dusk-to-dawn feature turns the lights on automatically when it gets dark outside – perfect for those long summer evenings or to ensure your safety.

Cool white light 4,000 K



Did you know that different shades of white light are identified by different colour temperatures, measured in Kelvin (K)? Lower colour temperatures produce a warm, cosy white light, while higher colour temperatures produce a cool, more energising white light. This luminaire produces cool white light at 4,000 K.

Specifications

Design and finishing

- Colour: Black
- Material: Metal, Plastic

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Centrepiece: No

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED innovations: UltraEfficient
- Extra Features: Dusk to dawn, Sensor, Solar, Water Resistant

Power consumption

- Power: 3.2

Product dimensions and weight

- Net weight: 1.5606 kg
- Overall height: 280 mm
- Overall length: 190 mm
- Overall width: 200 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 500/25
- Bulb technology: LED
- Light colour: Cool white light
- Mains power: DC 4
- Fixture dimmable: No
- IP code: IP44
- Class of protection: Class III – Safe Extra Low Voltage
- Light source replaceable: Yes
- Number of light sources: 1

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8720169361881
- Net weight: 1.53 kg
- Gross weight: 2 kg
- Height: 33.5 cm
- Length: 23.5 cm
- Width: 23.5 cm



Issue date: 2026-07-01
Version: 0.242

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com