

# PHILIPS

Lois Wall Lights  
50W

Outdoor luminaires

3000K

Black

Water Resistant



8720169365148



## Powerful light, long-lasting quality

Philips Lois outdoor floodlights provide powerful light with durable design, to provide long-lasting brightness for your garden.

### **Ease of use**

- A full range of available applications

### **Sustainable light solutions**

- Long lifetime up to 15,000 hours

### **Premium quality**

- High-quality aluminium and real glass

### **Designed for outdoors**

- IP65 weatherproof rated

### **High-quality light**

- High light output

# Highlights

## A full range of available applications

Ideal outdoor lighting for a garden, terrace, pathway or balcony, Philips outdoor wall, post, pedestal and ceiling lights create a cosy, relaxing atmosphere when the sun goes down, as well as providing the reassurance of being able to see safely after dark.

## Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

## High-quality aluminium and real glass



This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminium and real glass.

## IP65 weatherproof rated

An IP rating contains two digits which refer to protection against solids, such as dust, or liquids, such as rain. IP65 means that these light fixtures are protected against water splashed from any direction and are suitable for outdoor use.

## High light output

Brighten up your home with high-quality light

# Specifications

## Design and finishing

- Colour: Black
- Material: Metal

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Anti-rust anti-dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No
- Centrepiece: No

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K

**Miscellaneous**

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

**Power consumption**

- Power: 50

**Product dimensions and weight**

- Net weight: 0.508 kg
- Overall height: 170 mm
- Overall length: 200 mm
- Overall width: 30 mm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Total lumen output fixture: 5400
- Bulb technology: LED
- Light colour: 3000
- Mains power: AC 220-240
- Fixture dimmable: No
- Energy class included light source: F
- IP code: IP65 | Dust-tight and jet-proof
- Class of protection: Class I – Earthed
- Light source replaceable: No
- Number of light sources: 1

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169365148
- Net weight: 0.52 kg
- Gross weight: 0.56 kg
- Height: 20.4 cm
- Length: 3.7 cm
- Width: 16.2 cm



Issue date: 2026-04-15  
Version: 0.233

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)