

Valen Ceiling Light
13W Square

Ceiling Lights

2200-6500 K

White

Dimmable; Remote Control;
Tunable White; Warm Glow

8720169385191



Set your desired ambience at your fingertips

With just a few simple clicks on the remote control, the Philips LED All-in-one ceiling light gives you the ultimate flexibility and convenience to personalise your light settings with ease. Comfortable light that's easy on your eyes. Create the desired ambience with lights that know your needs.

High-quality light

- EyeComfort – light that's easy on your eyes

Match your interior

- Super slim design

Easy to experience

- Easy installation

Control

- Enhance your moment. Tunable with dimming functions (remote control included)
- Adjustable colour temperature and brightness

Highlights

EyeComfort – light that's easy on your eyes



Poor-quality light can cause eye strain. With many people spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour

rendition and dimming effects to ensure that they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of its lifespan, delivering consistent light quality, output and colour for more than a decade.

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

Enhance your moment. Tunable with dimming functions (remote control included)

Easy-to-use remote control lets you dim to the perfect light level for your mood.

Adjustable colour temperature and brightness

Changing colour temperature and brightness allows you to change the mood and atmosphere in a room, matching the light to different kinds of activity.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Colour: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2200–6500 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 119 lm/W

Miscellaneous

- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Remote control, Tunable White, WarmGlow

Other characteristics

- Lamp current: 117 mA

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 1.2 kg
- Overall height: 40 mm
- Overall length: 300 mm
- Overall width: 300 mm

Service

- Warranty: 5 year(s)

Packaging dimensions and weight

- EAN/UPC - product: 8720169385191
- Net weight: 1.05 kg
- Gross weight: 1.25 kg
- Height: 30 cm
- Length: 6.2 cm
- Width: 30 cm

Technical specifications

- Total lumen output fixture: 1550 (@2700K)
- Light colour: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated



Issue date: 2025-12-06
Version: 0.278

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com