

# PHILIPS

Filament Bulb Clear  
60 W A60 E27 x3

LED

2700 K

806 lm

15000 h



8721103047441



## Bright LED lighting

Philips LED light bulbs provide high-quality light, with a long life and immediate, significant energy savings.

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Create the right light for your home

- A simple LED for everyday use

# Highlights

## Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 330
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Luminous efficacy (rated) (nom.): 115

## Miscellaneous

- EyeComfort: No

## Packaging information

- EAN: 8721103047441
- EOC: 872110304744100
- Product title: LED classic 60W A60 E27 WW CL ND 3CT/4EC

## Power consumption

- Power factor: 0.51
- Voltage: AC 220-240 V
- Wattage equivalent: 60
- Energy efficiency label (EEL): E
- Power: 7
- Energy consumption kWh/1,000 hours: 7

## Product dimensions and weight

- Overall height: 104 mm
- Overall length: 104 mm
- Overall width: 60 mm

## Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 2136336
- Can it be used in closed luminaires: No

## The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 8721103047441
- Net weight: 0.1 kg
- Gross weight: 0.15 kg
- Height: 12.2 cm
- Length: 6.7 cm
- Width: 19.1 cm



Issue date: 2026-04-15  
Version: 0.266

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)