

PHILIPS

Filament Bulb Clear
60 W A60 E27 x6

LED

2700 K

806 lm

15000 h



8721103047465



Bright LED lighting

Philips LED light bulbs provide high-quality light, with a long life and immediate, significant energy savings.

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Create the right light for your home

- A simple LED for everyday use

Highlights

Replaces standard incandescents



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No
- Lamp Finish: Clear
- Bulb material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 330 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Luminous efficacy (rated) (nom.): 115 lm/W

Miscellaneous

- EyeComfort: No

Packaging information

- EAN: 8721103047465
- EOC: 872110304746500
- Product title: LED classic 60W A60 E27 WW CL ND 6CT/4EC

Power consumption

- Power factor: 0.51
- Voltage: AC 220–240 V
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): E
- Power Consumption: 7 W
- Energy consumption kWh/1,000 hours: 7

Product dimensions and weight

- Overall height: 104 mm
- Overall length: 104 mm
- Overall width: 60 mm

Technical specifications

- Frequency: 50–60
- EPREL Registration Number: 2136335
- Can it be used in closed luminaires: No

Packaging dimensions and weight

- EAN/UPC – product: 8721103047465
- Net weight: 0.2 kg
- Gross weight: 0.28 kg
- Height: 12.2 cm
- Length: 13 cm
- Width: 19.3 cm



Issue date: 2025-11-22
Version: 0.304

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com