

PHILIPS

Filament Candle
Amber 25 W B35 E14

LED

2200 K

270 lm

15000 h

Dimming



8721103048950



Decorate your home with natural light

Both decorative and functional, this light bulb has an elegant, vintage design with a visible spiral filament and provides bright, natural light with excellent colour rendering. Start saving energy right away with a bulb that will last for 15,000 hours.

High-quality light

- Designed for the comfort of your eyes

High-quality LED light that lasts for decades

- Light that shows true colours

Designed to be seen, looks good on and off

- Classic glass LED

Vintage bulb design with spiral filament

- This is a light designed for beauty and performance, with a vintage design and a visible spiral filament. Bring a touch of style and elegance to any room, whether the light is switched on or off.

High-performance spiral slim filament

- The delicate spiral filament adds to the bulb's aesthetic appeal. Create a warm and welcoming atmosphere with soft and natural light that offers excellent colour rendering at CRI 90.

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go

easy on the eyes, and create the perfect ambience for your home.

Light that shows true colours



See the true colours of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colours match perfectly.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Vintage bulb design

High-performance slim filament

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Lamp Finish: Amber
- Dimmable: Yes
- Bulb material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 300
- Colour rendering index (CRI): 90
- Colour temperature: 2200 K
- Nominal luminous flux: 270 lm
- Luminous efficacy (rated) (nom.): 87

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Decorative, Dimmable

Packaging information

- EAN: 8721103048950
- EOC: 872110304895000
- Product title: LED B35 25W 2200K E14 Amber SP DIM 1PF/4

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 25
- Energy efficiency label (EEL): F
- Power: 3.1
- Energy consumption kWh/1,000 hours: 4

Product dimensions and weight

- Overall height: 98 mm
- Overall length: 98 mm
- Overall width: 35 mm

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 2209192
- Can it be used in closed luminaires:
No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8721103048950
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 6.3 cm



Issue date: 2026-04-15
Version: 0.223

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com