

PHILIPS

Remote Control Ceiling Light 24W

Ceiling Lights

4000/6500/2700 K

White

Dimmable; Remote Control;
Tunable White

8721103055927



Set your desired ambience at your fingertips

With just a few simple clicks on the remote control, the Philips LED All-in-one ceiling light gives you the ultimate flexibility and convenience to personalise your light settings with ease. Comfortable light that's easy on your eyes. Create the desired ambience with lights that know your needs.

Easy to experience

- Easy installation

Light effect

- SceneSwitch colour change
- Uniform light distribution

Premium quality

- EyeComfort – light that's easy on the eyes

Control

- Convenient brightness control-step dimming function (remote control included)

Highlights

Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

SceneSwitch colour change

SceneSwitch Colour Change lets you set the overall mood of a living space at home. Stay focused with cool daylight, be more productive with cool white light or wind down and relax with warm white light. In essence, consumers can control the lights in their home according to their daily activities.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Convenient brightness control-step dimming function (remote control included)

Shift between different levels of brightness to match your mood or activity.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: White
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 15,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700-4000-6500 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 100 lm/W

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, Remote control, Tunable White

Other characteristics

- Lamp current: 198 mA

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.84 kg
- Overall height: 60 mm

Service

- Warranty: 5 year(s)

Packaging dimensions and weight

- EAN/UPC – product: 8721103055927
- Net weight: 0.84 kg
- Gross weight: 1.05 kg
- Height: 35 cm
- Length: 34.5 cm
- Width: 8 cm

Technical specifications

- Diameter: 300 mm
- Total lumen output fixture: 2400
- Light colour: 4000/6500/2700
- Mains power: AC 220–240
- Fixture dimmable: Yes
- IP code: IP20
- Class of protection: Class I – Earthed



Issue date: 2025-08-30
Version: 0.286

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com