

# PHILIPS

## Desk Light

Desk Lights

3000K

White

Dimmable

8721103108098



## Superior light and style

Make any room glow in your favourite colour

### **Durability**

- Long life span up to 15,000 hours

### **Create the perfect atmosphere**

- Enjoy high-quality light that's easy on your eyes and easily adjust the brightness to suit each moment; with a minimalist slim design, the Philips Cilantro spotlight works with almost any decor.

# Highlights

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

## Create the perfect atmosphere

Enjoy high-quality light that's easy on your eyes and easily adjust the brightness to suit each moment; with a

minimalist slim design, the Philips Cilantro spotlight works with almost any decor.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: White
- Material: Metal

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Living Room
- Style: Modern
- Type: Desk Lights
- EyeComfort: No
- Extra Features: Dimmable

## Product dimensions and weight

- Net weight: 0.451 kg
- Overall height: 32 mm
- Overall length: 12 mm
- Overall width: 10 mm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 120
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: DC 4.2
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III – Safe Extra Low Voltage

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

## Packaging dimensions and weight

- EAN/UPC – product: 8721103108098
- Net weight: 0.9 kg
- Gross weight: 1.1 kg
- Height: 7.5 cm
- Length: 28.5 cm
- Width: 14.5 cm



Issue date: 2026-04-15  
Version: 0.82

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)