

# PHILIPS

Smart Dial Switch, Convenient Controls, Dimming, Rechargeable Battery

Smart accessory

Customisable buttons

Wall-mountable and remote

Works without Wi-Fi



8721103136039



## All-in-one switch

Control your lighting effortlessly with a sleek smart dial switch featuring a smooth rotary control for on/off and dimming, plus two programmable buttons for instant access to your favourite light modes. Customise the buttons in the WiZ app to create personalised shortcuts, then mount the compact base on the wall or detach the magnetic dial for portable, wireless control whenever you need it. The switch communicates directly with your lights, so it works reliably even without Wi-Fi, while a subtle LED ring shows when lights are active or when the USB-rechargeable battery needs a boost. Easy to set up using the WiZ app and fully compatible with all Connected by WiZ products.

### Easy setup

- Setting up couldn't be easier

### Smart control

- Wide range
- Connected by WiZ
- Customisable scenes

### Form factor

- Convenient controls

# Highlights

## Setting up couldn't be easier

Download the WiZ app, connect your device to the power and then connect it to your Wi-Fi network. And now you can start using it!

## Wide range

Control lights and devices within a range of 15 metres in any normal indoor environment with partitions and walls.

## Connected by WiZ

Fully compatible with all Connected by WiZ products – use the WiZ app to set up and unlock all the benefits of smart lighting.

## Customisable scenes

For extra convenience, you can customise four lighting scenes in the WiZ app. Alternate between your perfect ambience with a short-press or long-press.

## Convenient controls

Mount the base anywhere and detach the remote for wireless lighting control whenever you need it.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: White
- Material: Plastic

## Extra feature/accessory incl.

- Batteries included: Yes
- Control distance: 15 m

## Power consumption

- Voltage: 5 V

## Product dimensions and weight

- Net weight: 0.1 kg
- Cut out length: 86 cm
- Cut out width: 86 cm
- Overall height: 2.49 mm
- Overall length: 8.6 mm
- Overall width: 8.6 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Battery type: LP402030
- IP code: IP20
- Class of protection: Class III – Safe Extra Low Voltage

## What's supported

- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android

## Packaging dimensions and weight

- EAN/UPC – product: 8721103136039
- Net weight: 0.1 kg
- Gross weight: 0.14 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 10.6 cm



Issue date: 2026-06-10  
Version: 0.158

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)