

# PHILIPS

## Squire Lite LED Table Lamp, Black

Smart LED

Easy ambient lighting

Static and dynamic light modes

Syncable with TV and music



8721103158932



## Splashes of colour

Add atmosphere to any room with stunning wall-washing light effects that you can customise. Enjoy full-colour and tunable white light in a compact design that complements any decor. Easy to set up using the WiZ app, fully compatible with all Connected by WiZ products and Matter-certified for seamless integration with smart home assistants like Alexa, Apple Home and Google Home. Charge using the USB-C cable provided (no AC adapter included).

### Easy setup

- Set-up couldn't be easier

### Smart features

- Easy ambience
- Immersive light effects
- SpaceSense motion detection

### Smart devices

- Matter-certified

### Light modes

- Tunable white light

### Form factor

- Sleek design

# Highlights

## Set-up couldn't be easier




1. Download the WiZ app  
2. Switch on your light  
3. Connect the light to Wi-Fi

## Easy ambience



Fill your space with vibrant colour using static and dynamic light modes that you can customise to suit your mood.

## Immersive lighting



Transform your home entertainment experience by syncing your lights with music and video – syncing hardware required.

## SpaceSense motion detection




Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WiZ lights or devices.

## Matter-certified




Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

## Tunable white light



Easily adjust from cool, blueish hues (6,500 K) that enhance visibility and focus to soft, warmer tones (2,200 K) for relaxing in the evening.

## Sleek design



Available in both black and white, this stylish little light is designed to blend seamlessly with any home decor.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: Black
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your colour: Yes
- Dimmable with remote control: Yes
- Fully weatherproof: No
- LED integrated: Yes
- On/off switch on wire: No
- Remote control included: No
- Solar Energy: No
- Warm glow dimmable light: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI):  $\geq 80$
- Colour temperature: 2700/6500
- Warm-up time to 60% light:  $< 2$
- Luminous efficacy (rated) (nom.): 65

## Miscellaneous

- Especially designed for: Bedroom, Dining Room, Living Room, Children's room
- EyeComfort: Yes

## Power consumption

- Voltage: 5 V
- Energy consumption kWh/1,000 hours: 8.5

## Product dimensions and weight

- Net weight: 0.37 kg
- Overall height: 13.4 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 134 mm
- Total lumen output fixture: 550lm@4000K
- Bulb technology: LED
- Light colour: Coloured and white light (RGBW)
- Wattage bulb included: 8.5
- IP code: IP20
- Class of protection: Class III – Safe Extra Low Voltage

## The bulb

- Software upgradable: Yes

## What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

## Packaging dimensions and weight

- EAN/UPC - product: 8721103158932
- Net weight: 0.37 kg
- Gross weight: 0.45 kg
- Height: 15 cm
- Length: 13.5 cm
- Width: 13.5 cm



Issue date: 2026-06-13  
Version: 0.267

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)