

# PHILIPS

## Halogen capsule bulb

Halogen

42 W (60 W)

G9

Warm white

Dimmable



8727900252910



## Stunning sparkling light

Philips Halogen capsule bulbs provide crisp, sparkling halogen light, bringing out the best in your luminaire. All Philips Halogen products are fully dimmable.

### Superior light quality

- Dimmable
- Sparkling natural light

# Highlights

## Dimmable

You control the level of light you need. Dimmable with all dimmers, this Philips halogen bulb can be adjusted from a bright, sparkling light to a warm, cosy glow.

## Sparkling natural light



This Philips capsule bulb provides a sparkling, natural halogen light. Use capsule light bulbs to enhance the beauty of your luminaire.

# Specifications

## Bulb characteristics

- Lamp shape: Non-directional capsule
- Socket: G9
- Technology: Halogen
- Dimmable: Yes
- Lamp Finish: Clear

## Lamp dimensions

- Diameter: 13 mm
- Height: 45 mm
- Width: 13 mm

## Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Lumen maintenance factor: 0.8
- Number of switch cycles: 8,000
- Nominal lifetime: 2,000

## Light characteristics

- Application: Special application, Accent light
- Colour rendering index (CRI): 100
- Colour temperature: 2800 K
- Light Colour Category: Warm White
- Nominal luminous flux: 630 lm
- Starting time: 0 s
- Warm-up time to 60% light: Instant full light s
- Correlated Colour Temperature (Nom): 2800 K
- Luminous Flux: 630 lm
- Luminous efficacy (rated) (nom.): 15 lm/W

## Other characteristics

- Lamp current: not applicable mA

## Power

- Power Factor (Fraction): 1

## Power consumption

- Power factor: 1
- Voltage: 230 V
- Wattage: 42 W
- Wattage equivalent: 60 W
- Power Consumption: 42.0 W
- Energy consumption kWh/1,000 hours: 42

## Rated values

- Rated beam angle: not applicable degree(s)
- Rated lifetime: 2,000
- Rated luminous flux: 630 lm
- Rated peak intensity: not applicable cd
- Rated power: 42 W

## Technical specifications

- Dimmable: Yes
- Cap base: G9

## Packaging dimensions and weight

- EAN/UPC - product: 8727900252910
- Net weight: 3.3 g
- Gross weight: 10.4 g
- Height: 12 cm
- Length: 1.3 cm
- Width: 14 cm



Issue date: 2025-10-22  
Version: 0.879

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)