

PHILIPS

Table lamp

66110RobotPlus

blue

LED



66110/35/R3



Advanced desk lighting for a brighter future

Philips RobotPlus LED desk light creates a well-illuminated learning environment for your productivity. Designed with advanced optical technologies and honeycomb lenses, RobotPlus provides an enhanced visibility and reduces harmful glares.

Light effect

- Even light distribution
- Honeycomb optics

Special characteristics

- Flexible arm

Control

- 4-level step dimming with mode indicator

Highlights


Even light distribution



Honeycomb optics

Light is diffused through an array of multiple micro honeycomb lenses for uniform light output that reduces indirect glare and provides comfortable light on your space.

Flexible arm



Direct the light to where you really need it thanks to the flexible arm.

4-level step dimming with mode

Intuitive 4-level brightness control setting with mode indicator provides gives you greater light control.

Specifications

Design and finishing

- Color: Blue
- Material: Aluminium

Extra feature/accessory incl.

- FFP – Frustration Free Pack: Yes

Miscellaneous

- Especially designed for: Home office & Study, Living- & Bedroom
- Type: Table Lamp
- EyeComfort: No

Product dimensions and weight

- Net weight: 2.240 kg
- Height: 42 cm
- Length: 16 cm
- Width: 36.7 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 800 lm
- Mains power: Range 100 V – 240 V, 50–60 Hz
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: -
- Maximum wattage replacement bulb: 9.2 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC – product: 8718696170335
- Net weight: 2.24 kg
- Gross weight: 2.51 kg
- Height: 455 mm
- Length: 206 mm
- Width: 206 mm
- Material number (12NC): 915005708001



Issue date: 2024-04-20
Version: 0.99

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com