

# PHILIPS

Ceiling Light 55W  
Square

Ceiling Lights

2700-6500K

Grey

Dimmable



6922341910173



## Set your desired ambiance at your fingertips

Create the right ambience every time. With just a couple of clicks on the remote control, Philips LED all-in-one ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Color: Grey
- Material: Metal

## Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700-6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 72 lm/W

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 285 mA

## Product dimensions and weight

- Net weight: 3.4 kg
- Overall height: 95 mm
- Overall length: 593 mm
- Overall width: 593 mm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 4000
- Light color: 2700-6500
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I - Earthed

## Packaging dimensions and weight

- Net weight: 3.4 kg
- Gross weight: 4.8 kg
- Height: 0
- Length: 0
- Width: 0



Issue date: 2025-08-30  
Version: 0.150

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)