

PHILIPS

Ceiling Light 55W
Square

Ceiling Lights

2700-6500K

Grey

Dimmable



6947830485338



Set your desired ambiance at your fingertips

Create the right ambience every time. With just a couple of clicks on the remote control, Philips LED all-in-one ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment

Easy to experience

- Enhance your momentTunable with memory function
- 10s time delay light off with remote control

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Tunable with wall switch
- 4 pre-set scenes
- Auto shutdown after 60 mins
- Convenient brightness controlLinear dimming function (remote control not included)

Highlights

Enhance your momentTunable with memory function

Memorize your favorite tunings of different light settings to easily find your perfect level of illumination.

10s time delay light off with remote control

The 10 second delay gives you time to leave the room once you've turned out the light with your remote.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Tunable with wall switch

An easy-to-use wall switch allows you to shift between different light colors.

4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

Auto shutdown after 60 mins

When sleep mode is on, the light will automatically go out after 60 minutes. No more getting up in the middle of the night just to switch the light off.

Convenient brightness controlLinear dimming function (remote control not included)

Lets you smoothly shift between different brightness levels to find the perfect mood.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Rectangle
- Dimmable: Yes

Design and finishing

- Color: Grey
- Material: Metal, Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Lamp current: 300 mA
- Efficacy: 67 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 3.1 kg
- Height: 8.2 cm
- Length: 56 cm
- Width: 56 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 3700
- Light color: 2700-6500
- Mains power: AC 220-240
- IP code: IP20
- Class of protection: Class I – Earthed

Packaging dimensions and weight

- Net weight: 3.1 kg
- Gross weight: 4.6 kg
- Height: 0
- Length: 0
- Width: 0



Issue date: 2025-06-16
Version: 0.97

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com