

PHILIPS

Fan Ceiling Light
48+24W

Fan Ceiling Lights

3000-5700K

White

Remote Control



6947939188017



One fixture. Your switch. Three light settings.

Combine customizable light with a comfortable breeze with the Philips LED retractable ceiling fan light, which includes a remote control. With transparent blades that retract out of sight when not in use and three SceneSwitch light settings, this light creates the perfect atmosphere in any space.

Easy to experience

- Retractable ceiling fan with transparent blades
- Easy to install, safe to use
- Powerful, reliable performance

Ambient light effect

- Bright yet comfortable ceiling light

Premium quality

- Quiet motor

Control

- The remote control offers easy control of all the functions of the ceiling fan and light. Switch the light or fan on or off, choose from three fan speeds, cycle through SceneSwitch light settings, use the flashlight feature, or set one of five timers.

Mounting

- Easy to install, safe to use

Highlights

Retractable ceiling fan with transparent blades

Say goodbye to spinning shadows on the ceiling: this fan has transparent blades that can be folded into the light and out of sight when not in use.

Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

Powerful, reliable performance

The Philips LED ceiling fan light is designed to ensure powerful air circulation and continued reliability over time. Its wide blade design allows a large coverage of air volume to ensure maximum airflow for cooling.

Bright yet comfortable ceiling light

The Philips LED ceiling fan light offers powerfully bright — yet comfortable — light for your home, which you can control with the included remote control or a wall switch.

Quiet motor

The Philips LED ceiling fan light offers a quiet motor, circulating the air in the room without any loud noises.

Remote control included

The remote control offers easy control of all the functions of the ceiling fan and light. Switch the light or fan on or off, choose from three fan speeds, cycle through SceneSwitch light settings or timers.

Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Stainless Steel

Durability

- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- Extra Features: Remote Control

Other characteristics

- Lamp current: 385 mA
- Efficacy: 66 lm/W

Product dimensions and weight

- Net weight: 8 kg
- Height: 40 cm
- Length: 41 cm
- Width: 41 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 410 mm
- Total lumen output fixture: 1600
- Light color: 3000-5700
- Mains power: 220
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 48+24
- IP code: IP20
- Class of protection: Class I



Issue date: 2024-10-01
Version: 0.240

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com