

# PHILIPS

Wincel Ceiling Light  
24W

Ceiling Lights

2700-6500K

White

Dimmable;Remote Control



8720169196117



## Set your desired ambiance at your fingertips

With just a few simple clicks on the remote control, Philips LED All-in-one ceiling light gives you the ultimate flexibility and convenience to personalize your light settings with ease. Comfortable light that's easy on your eyes. Create desired ambiances with light that knows your needs.

### Premium quality

- EyeComfort - light that's easy on the eyes

### Control

- Tunable - from warm white to cool daylight
- Brightness control with memory function
- 4 pre-set scenes
- Remote control provides easy control of light settings up to 10M
- Wall-mountable remote control

# Highlights

## **Eyecomfort**

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## **Tunable - from warm white to cool daylight**

Tunable lighting lets you change the color of light to match your mood or activity. Warm white is ideal for relaxation, cool daylight for invigorating focus.

## **Brightness control with memory function**

Memorizes the specific brightness levels you prefer.

## **4 pre-set scenes**

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

## **Remote control provides easy control of light settings up to 10M**

Turn lights on or off or change brightness and color from up to 10m away with this remote control.

## **Wall-mountable remote control**

With the included bracket, you can mount your remote wherever you need an additional switch—no wiring required.

# Specifications

## **Bulb characteristics**

- Intended use: Indoor
- Lamp shape: Round

## **Design and finishing**

- Color: White
- Material: Plastic

## **Durability**

- Average life (at 2.7 hrs/day): 20 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

## **Environmental**

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## **Extra feature/accessory incl.**

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

## **Light characteristics**

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## **Miscellaneous**

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Remote Control

## **Other characteristics**

- Lamp current: 210 mA
- Efficacy: 104 lm/W

## **Power consumption**

- Power factor: 0.5

#### Product dimensions and weight

- Net weight: 0.8 kg
- Height: 7 cm
- Length: 39.5 cm
- Width: 39.5 cm

#### Service

- Warranty: 5 year(s)

#### Technical specifications

- Lifetime up to: 20,000 hour(s)
- Diameter: 395 mm
- Total lumen output fixture: 2500
- Light color: 2700-6500
- Mains power: AC 220-240
- Fixture dimmable: Wireless Dim - Do not use with dimmer
- LED: Yes
- IP code: IP20
- Class of protection: Class I

#### Packaging dimensions and weight

- EAN/UPC - product: 8720169196117
- Net weight: 0.79 kg
- Gross weight: 1.44 kg
- Height: 9.6 cm
- Length: 47.8 cm
- Width: 48.5 cm



Issue date: 2025-03-04  
Version: 0.369

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)