PHILIPS

Valen Ceiling Light 16W

Ceiling Lights

2200-6500K

White

Dimmable;Remote Control;Tunable White;WarmGlow

8720169385139

Set your desired ambiance at your fingertips

With just a few simple clicks on the remote control, Philips LED All-in-one ceiling light gives you the ultimate flexibility and convinience to personalize your light settings with ease. Comfortable light that's easy on your eyes. Create desired ambiances with light that knows your needs.

High quality light
- EyeComfort – light that's easy on your eyes

Match your interior
- Super slim design

Easy to experience
- Easy installation

Control
- Enhance your moment. Tunable with dimming functions (remote control included)
- Adjustable color temperature and brightness

Highlights

EyeComfort – light that's easy on your eyes

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. This Philips LED luminaire not only delivers comfortable light, but also stays that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade.

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Enhance your moment. Tunable with dimming functions (remote control included)

Easy to use remote control lets you dim to the perfect light level for your mood.

Adjustable color temperature and brightness

Changing color temperature and brightness allows you to change the mood and atmosphere in a room, matching the light to different kinds of activity.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Batteries included: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200-6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 125 lm/W

Miscellaneous

- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, Remote Control, Tunable White, WarmGlow

Other characteristics

- Lamp current: 140 mA

Power consumption

- Power factor: 0.5

Product dimensions and weight
- Net weight: 0.8 kg
- Overall height: 20 mm

Service
- Warranty: 5 year(s)

Technical specifications
- Diameter: 291 mm
- Total lumen output fixture: 2000 (@2700K)
- Light color: 2200-6500K
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class II - Double Insulated

Packaging dimensions and weight
- EAN/UPC - product: 8720169385139
- Net weight: 0.8 kg
- Gross weight: 0.97 kg
- Height: 29.5 cm
- Length: 4.8 cm
- Width: 29.5 cm

Issue date: 2025-09-20
Version: 0.284

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com