

# PHILIPS

Light Strip Light  
Strip 50m

Light Strips

4000K

Transparent

8720169376113



## Durable and bright

Bright and even light

### Durability

- Long life span up to 15,000 hours

# Highlights

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Transparent
- Material: Plastic

## Durability

- Number of switch cycles: 7,500
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Warm-up time to 60% light: 2

## String light/Lightstrip

- Extendibility: No

## Miscellaneous

- Especially designed for: Living Room
- Style: Contemporary
- Type: Light Strips
- EyeComfort: No

## Other characteristics

- Lamp current: 1870 mA

## Power consumption

- Power factor: 0.95

## Product dimensions and weight

- Net weight: 3.3 kg
- Overall height: 5.5 mm
- Overall length: 50,000 mm
- Overall width: 10.5 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Total lumen output fixture: 700
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP65 | Dust-tight and jet-proof, IP20 | Finger-protected
- Class of protection: Class II - Double Insulated

## Packaging dimensions and weight

- Net weight: 2.81 kg
- Gross weight: 2.81 kg
- Height: 0
- Length: 0
- Width: 0



Issue date: 2025-08-30  
Version: 0.99

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)