

# PHILIPS

## Wall light

Linea

31095 TrunkLinea 7W 4000K

white

LED



31095/31/66



## Light and relaxed

Philips myLiving Decolinea Trunk LED batten cove light is all about performance. Shadow free and connectable up to 12 pieces at a time. Available in 4 lengths and up to 15,000 hours usage, it is the ideal replacement of the T5 batten.

### Easy installation

- Easy installation

### Long lifespan

- Extremely long life 20,000 hours

### Energy saving

- Built-in LED, as part of the system

# Highlights

## Easy installation



No more hassle in installation. Just fix or hang securely on the wall and plug in, now this luminaire is ready to light on.

## Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement

while having the perfect light ambiance in your home.

## Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

# Specifications

## Design and finishing

- Color: White
- Material: Synthetic

## Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes

## Miscellaneous

- Especially designed for: Living- & Bedroom, Home office & Study
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No

## Product dimensions and weight

- Net weight: 0.145 kg
- Height: 3.6 cm
- Length: 58.4 cm
- Width: 2.2 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 500 lm
- Mains power: Range 220 V - 240 V, 50-60 Hz
- LED: Yes
- Built in LED: Yes
- Number of bulbs: 1
- Wattage bulb included: 6 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

## Packaging dimensions and weight

- EAN/UPC - product: 6947830426348
- Net weight: 0.14 kg
- Gross weight: 0.18 kg
- Height: 24 mm
- Length: 38 mm
- Width: 590 mm
- Material number (12NC): 915004986201



Issue date: 2024-07-15  
Version: 0.316

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)