

# PHILIPS

## Wall light

### Linea

31168 Algebra

white

LED



31168/31/86



## Bring imagination to light

Connect and extend your illumination with Philips myLiving Linea wall and ceiling light. Its white synthetic body houses integrated LED to provide high quality luminance. It is easy to install and can be connected with multiple units.

### Light effect

- Even light distribution

### Long lifespan

- Extremely long life 20,000 hours

### Energy saving

- Built-in LED, as part of the system

### Energy efficient

- 80% energy saving, compared to traditional light sources

# Highlights

## Even light distribution



## Integrated LED light source



## Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

## 80% energy saving



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

# Specifications

## Design and finishing

- Color: White
- Material: Synthetic

## Durability

- Nominal lifetime: 15,000

## Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes

## Miscellaneous

- Especially designed for: Living- & Bedroom, Home office & Study
- Type: Wall Lights
- EyeComfort: No

## Product dimensions and weight

- Net weight: 0.373 kg
- Height: 4.3 cm
- Length: 60 cm
- Width: 7.0 cm

**Technical specifications**

- Total lumen output fixture: 2000 lm
- Mains power: 220 V, 50–60 Hz
- Wattage bulb included: 25 W
- Maximum wattage replacement bulb: 27
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: Class II – Double Insulated

- Number of light sources: 1

**Packaging dimensions and weight**

- EAN/UPC – product: 6947830431359
- Net weight: 0.37 kg
- Gross weight: 0.54 kg
- Height: 60 mm
- Length: 97 mm
- Width: 619 mm



Issue date: 2025-06-13  
Version: 0.192

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)