

PHILIPS

Meranti Ceiling/Wall Spotlight 2x

Ceiling/Wall Spotlights

No bulb

Matt chrome



50312/17/E7



The accent on style

Include this practical Philips spotlight in your home. Choose your Philips GU10 LED bulb to go with your spot style and ensure a high quality and long lasting light.

Special characteristics

- Adjustable spot head
- No bulb included

Highlights

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

No bulb included

This lamp comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long lasting light output.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Chrome
- Material: Glass

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Adjustable - rise and fall
- LED integrated: No
- Mount product out of arms reach: Yes

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Hall
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.333 kg
- Overall height: 100 mm
- Overall length: 285 mm
- Overall width: 155 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: No bulb included
- Mains power: AC 220-240
- Energy class included light source: no bulb included
- Fitting/cap: GU10
- Wattage bulb included: 35W
- Maximum wattage replacement bulb: 35
- IP code: IP20 | Finger-protected
- Class of protection: Class I - Earthed
- Light source replaceable: Yes
- Number of light sources: 2

Packaging dimensions and weight

- EAN/UPC - product: 8718696133255
- Net weight: 0.33 kg
- Gross weight: 0.62 kg
- Height: 32 cm
- Length: 12 cm
- Width: 14 cm



Issue date: 2025-11-01
Version: 0.690

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com