

PHILIPS

Downlight

Functional

JB Downlight

White

8718696168684



Comfortable LED light that's easy on your eyes

Philips Essential LED ceiling light brightens up your room in a soft and uniform light with long-lasting LED technology. Perfect for lighting up any general spaces like rooms, balcony, kitchen and bathroom.

Easy to experience

- Easy installation

Light effect

- Uniform light distribution

Premium quality

- EyeComfort - light that's easy on the eyes

Highlights

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips

s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions and weight

- Net weight: 0.034 kg
- Cut out length: 4.3 cm
- Cut out width: 43 cm
- Height: 3.4 cm
- Length: 7.5 cm
- Width: 7.5 cm

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 75 mm
- Total lumen output fixture: 240
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 3
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718696168684
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 8 cm
- Length: 10.5 cm
- Width: 3.8 cm
- Material number (12NC): 929003530101



Issue date: 2024-07-25
Version: 0.55

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com