



# Comfortable LED light that's easy on your eyes

Philips Essential LED ceiling light brightens up your room in a soft and uniform light with long-lasting LED technology. Perfect for lighting up any general spaces like rooms, balcony, kitchen and bathroom.

# Easy to experience

· Easy installation

#### **Light effect**

· Uniform light distribution

#### **Premium quality**

• EyeComfort - light that's easy on the eyes

# Highlights

## Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

# **Uniform light distribution**

Throw light across your rooms in an even and uniform manner.

#### **Eyecomfort**

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip

s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

# **Specifications**

# Design and finishing

Color: WhiteMaterial: Plastic

#### **Durability**

· Nominal lifetime: 15,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### Extra feature/accessory incl.

· Dimmable with remote control: No

· LED integrated: Yes

· Remote control included: No

#### **Light characteristics**

Beam angle: 120 degree(s)Color rendering index (CRI): 80

### Miscellaneous

• Especially designed for: Living Room

# Product dimensions and weight

Net weight: 0.034 kg
Overall height: 34 mm
Overall length: 75 mm
Overall width: 75 mm

• Recessed Ceiling cutout: 43 cm x 4.3

## **Technical specifications**

· Diameter: 75 mm

Total lumen output fixture: 240

Light color: Green lightMains power: 220-240Fixture dimmable: No

Wattage bulb included: 3IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

# Packaging dimensions and weight

• EAN/UPC - product: 8718696169162

Net weight: 0.03 kgGross weight: 0.05 kg

Height: 8 cmLength: 10.5 cmWidth: 3.8 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips