



The new Shape of Style

Reimagine your world with Philips HexaStyle downlights, which have a unique hexagonal shape with a round fitment for easy installation. These downlights give you the freedom to embrace your creativity by arranging them in any pattern and configuration, and design your space your way!

Match your interior

- Expressive and elegant form
- Super slim design

Mounting

Patterned installation design

Durability

• Long life span up to 25,000 hours

Highlights

Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Patterned installation design

Attractive and memorable installation design with eye-catching pattern.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Design and finishing

Color: WhiteMaterial: Plastic

Durability

· Nominal lifetime: 25,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

Beam angle: 120 degree(s)Color rendering index (CRI): 80

· Color temperature: 4000 K

Miscellaneous

EyeComfort: Yes

Product dimensions and weight

Net weight: 0.15 kg
Overall height: 21 mm
Overall length: 178 mm
Overall width: 160 mm

ullet Recessed Ceiling cutout: 15.0 cm x

15.0 cm

Service

Warranty: 2 year(s)

Technical specifications

· Diameter: 178 mm

· Total lumen output fixture: 1200

Light color: 4000
Mains power: 220-240
Fixture dimmable: No
Wattage bulb included: 12
IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8719514437210

Net weight: 0.15 kgGross weight: 0.25 kg

Height: 4.5 cmLength: 23.6 cmWidth: 20.3 cm



Issue date: 2025-11-01 Version: 0.105 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.