

PHILIPS

Downlight

Functional

JB Downlight

White

8719514452770



Ease of installation

Philips LED downlights designed specifically to fit in 3 inch junction box as well as false ceiling; brightens up your room in a soft and uniform light output

Match your interior

- Compact size for small space

Easy to experience

- Easy installation

Premium quality

- EyeComfort - light that's easy on the eyes

Highlights

Compact size for small space

Perfect for fitting into small spaces

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they

meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120
- Color rendering index (CRI): 80
- Color temperature: 4000 K

Miscellaneous

- Especially designed for: Living Room

Product dimensions and weight

- Net weight: 0 kg
- Overall height: 30 mm
- Overall length: 106 mm
- Overall width: 106 mm
- Recessed Ceiling cutout: 8.0 cm x 8.0 cm

Technical specifications

- Diameter: 106 mm
- Total lumen output fixture: 490
- Bulb technology: LED
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 7
- IP code: IP20
- Class of protection: Class II - Double Insulated

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8719514452770
- Net weight: 0.05 kg
- Gross weight: 0.05 kg
- Height: 11.7 cm
- Length: 11.2 cm
- Width: 4.2 cm



Issue date: 2026-06-13
Version: 0.74

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com