

PHILIPS

Recessed spot light

Functional

GlideSpot

Black

8720169239258



Superior light and style

Premium Elegant COB light with decorative finishes which compliments the décor of the room, Metal heat sink helps in extended life

Designed for your living- and bedroom

- Create a stylish and welcoming atmosphere

Match your interior

- Decorative metallic finishing

Light effect

- Bright and focused beam

Material & finishing

- High quality metal material

Highlights

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define

the localised ambience you have always desired.

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

High quality metal material



Durable and attractive metal material for a strong finish.

Specifications

Design and finishing

- Color: White
- Material: Metal

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 30
- Color rendering index (CRI): 80
- Color temperature: 3000 K

Miscellaneous

- Especially designed for: Living Room

Product dimensions and weight

- Net weight: 0.14 kg
- Overall height: 56 mm
- Overall length: 77 mm
- Overall width: 77 mm
- Recessed Ceiling cutout: 6.7 cm x 6.7 cm

Technical specifications

- Diameter: 77 mm
- Total lumen output fixture: 475
- Bulb technology: LED
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 7
- IP code: IP20
- Class of protection: Class II - Double Insulated

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8720169239258
- Net weight: 0.14 kg
- Gross weight: 0.16 kg
- Height: 6.8 cm
- Length: 11 cm
- Width: 10 cm



Issue date: 2026-06-20
Version: 0.74

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com