

# PHILIPS

Recessed spot light

Functional

GlideSpot

Black

8720169239432



## Superior light and style

Premium Elegant COB light with decorative finishes which compliments the décor of the room, Metal heat sink helps in extended life

### Designed for your living- and bedroom

- Create a stylish and welcoming atmosphere

### Match your interior

- Decorative metallic finishing

### Light effect

- Bright and focused beam

### Material & finishing

- High quality metal material

# Highlights

## Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define

the localised ambience you have always desired.


## Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

## Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

## High quality metal material



Durable and attractive metal material for a strong finish.

# Specifications

## Design and finishing

- Color: White
- Material: Metal

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 30 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 4000 K

## Miscellaneous

- Especially designed for: Living Room

## Product dimensions and weight

- Net weight: 0.2 kg
- Overall height: 66 mm
- Overall length: 95 mm
- Overall width: 95 mm

## Technical specifications

- Diameter: 95 mm
- Total lumen output fixture: 900
- Light color: 4000
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 12
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

## Packaging dimensions and weight

- EAN/UPC – product: 8720169239432
- Net weight: 0.2 kg
- Gross weight: 0.25 kg
- Height: 7.2 cm
- Length: 13 cm
- Width: 11.2 cm



Issue date: 2025-08-30  
Version: 0.74

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)