



# Superior light and style

Premium Elegant COB light with decorative finishes which compliments the décor of the room, Metal heat sink helps in extended life

### Designed for your living- and bedroom

· Create a stylish and welcoming atmosphere

### Match your interior

· Decorative metallic finishing

### **Light effect**

· Bright and focused beam

### Material & finishing

· High quality metal material

### Highlights

### Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

### **Decorative metallic finishing**

Contemporary metallic finishing adds a modern touch.

### Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

### High quality metal material



Durable and attractive metal material for a strong finish.

## Specifications

### Design and finishing

Color: WhiteMaterial: Metal

### **Durability**

· Nominal lifetime: 15,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

### Extra feature/accessory incl.

• Dimmable with remote control: No

LED integrated: Yes

· Remote control included: No

### **Light characteristics**

Beam angle: 30 degree(s)Color rendering index (CRI): 80Color temperature: 6500 K

### Miscellaneous

Especially designed for: Living Room

### Product dimensions and weight

Net weight: 0.2 kgOverall height: 66 mmOverall length: 95 mmOverall width: 95 mm

• Recessed Ceiling cutout: 8.2 cm x 8.2

### **Technical specifications**

· Diameter: 95 mm

· Total lumen output fixture: 900

Light color: 6500Mains power: 220-240

• Fixture dimmable: No

• Wattage bulb included: 12

• IP code: IP20 | Finger-protected

 Class of protection: Class II - Double Insulated

### Packaging dimensions and weight

• EAN/UPC - product: 8720169239654

Net weight: 0.2 kgGross weight: 0.25 kg

Height: 7.2 cmLength: 13 cm

• Width: 11.2 cm



Issue date: 2025-11-01 Version: 0.74 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.