

# PHILIPS

Downlight

Functional

Full Glow Surface Light

White

8720169264298



## Hands-free light for safety & convenience

Philips rimless LED surface downlight can be easily turned on and off by the motion sensor. With a wide detection range, brighter light output and instant-on LED technology, you can be assured that your home space is well lit for security and visibility. Comfortable light that's easy on your eyes.

### Light effect

- Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

### Control

- Motion sensor

### Durability

- Long life span up to 15,000 hours

# Highlights

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

## Motion sensor

Detects when you enter and leave a room and turns lights off and on to save your electricity bills.

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional

## Product dimensions and weight

- Net weight: 0.185 kg
- Height: 4 cm
- Length: 14.5 cm
- Width: 14.5 cm

## Technical specifications

- Diameter: 145 mm
- Total lumen output fixture: 1500
- Light color: 3000
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 15
- IP code: IP20
- Class of protection: Class II - Double Insulated

## Packaging dimensions and weight

- EAN/UPC - product: 8720169264298
- Net weight: 0.19 kg
- Gross weight: 0.24 kg
- Height: 15.8 cm
- Length: 15.3 cm
- Width: 4.8 cm



Issue date: 2025-06-16  
Version: 0.64

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)