

PHILIPS

Downlight

Functional

Full Glow Striker

White

8720169270107



Comfortable light with a slimmer fit

Slim design surface light specially designed for smaller compact spaces like under cabinets

Designed for your living- and bedroom

- Create a stylish and welcoming atmosphere

Match your interior

- Compact size for small space

Premium quality

- EyeComfort - light that's easy on the eyes

Durability

- Long life span up to 15,000 hours

Highlights

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define

the localised ambiance you have always desired.

Compact size for small space

Perfect for fitting into small spaces

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Color: White
- Material: Plastic

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K

Miscellaneous

- Especially designed for: Living Room

Product dimensions and weight

- Net weight: 0.026 kg
- Overall height: 16 mm
- Overall length: 65 mm
- Overall width: 65 mm
- Recessed Ceiling cutout: 0 cm x 0 cm

Technical specifications

- Diameter: 65 mm
- Total lumen output fixture: 500
- Light color: 3000
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 5
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

Packaging dimensions and weight

- EAN/UPC – product: 8720169270107
- Net weight: 0.03 kg
- Gross weight: 0.03 kg
- Height: 2.8 cm
- Length: 6.8 cm
- Width: 6.8 cm



Issue date: 2025-09-03
Version: 0.74

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com