

PHILIPS

Grid & Cover


Switches & Sockets

Mirror Glaze

Grey

2 Module

913713947601



Reflect your style with Philips Mirror Glaze range

Philips Mirror Glaze range provides glassy finish plates for superior look.

Easy to use

- Front insertion & front removal
- Glossy finish
- Smooth curvy finish for easy maintenance
- Guiding locators
- Sleek design
- Easy installation

Safe to use

- Safe to use even with wet hands

Choose for a sustainable solution

- RoHS compliant

Durability

- Flexible cover frame

Convenience

- Wide range to choose from
- Suitable for most available boxes

913713947601

Strength

- Unique honeycomb construction

Highlights

Front insertion & front removal

Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Glossy finish

Glossy external finish for easy to clean and long lasting finish.

Smooth curvy finish for easy maintenance

Smooth curve and glossy finish doesn't not allowed dust to accumulate on surface and makes it easy to clean.

Guiding locators

Guiding locators provided in grid frame to guide the insert for easy installation.

Sleek design

Sleek Design so that the product doesn't come out too much from the wall.

Easy installation

Slot for Horizontal and vertical mounting/Hanging.

Safe to use even with wet hands

No seepage of water due to precision & covered design.

RoHS compliant

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

Flexible cover frame

Flexible cover frames which completely flushes well even with uneven walls.

Wide range to choose from

Different sizes available to meet customer requirement.

Suitable for most available boxes

Covers are designed in such a way that fits with most of the available installation boxes including the wooden boxes.

Unique honeycomb construction

Honeycomb construction provide the better strength to grid frames which last long.

Specifications

Design and finishing

- Color: Grey
- Material: PC
- Module/Gang: 2 Module
- Product Range: Mirror Glaze
- Minimum Installation Box Depth: 5 cm

Product dimensions and weight

- Length: 9.6 cm
- Width: 9.6 cm
- Depth: 1.52 cm

Service

- Warranty: 2 year(s)

Packaging dimensions and weight

- EAN/UPC - product: 8718696559208
- Net weight: 0.06 kg
- Gross weight: 0.06 kg
- Height: 1.5 cm
- Length: 9.6 cm
- Width: 9.6 cm



Issue date: 2026-05-13
Version: 0.103

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com