



# IP 44 fixtures ideal for gardens

Grey powder coated aluminium fixture. Sleek design. Warm white light

## Ease of use

· Moisture resistant

# **Light effect**

· Provides a bright white light

# Sustainable light solutions

· High quality LED light

# Beacon of trust

· You can trust what the Philips packaging is saying

# **Premium quality**

• Die-casted aluminum for a premium look and feel

# Highlights

Moisture resistant Superior light quality High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

## Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

#### **Premium materials**



# Specifications

#### **Bulb characteristics**

· Intended use: Outdoor

## Design and finishing

· Color: Grey

Material: Aluminium

#### **Durability**

• Nominal lifetime: 25,000

#### Extra feature/accessory incl.

- · Anti rust anti dust: Yes
- · Bi-directional light beams: Yes
- · Centerpiece: Yes
- Diffused light effect: Yes
- Fully weatherproof: Yes
- · LED integrated: Yes
- · Made for LED only: Yes
- Perfectly suited for up/down mounting: Yes
- Photometric data available: Yes
- Premium quality material: Yes
- Resistant high quality material: Yes
- Warm White Light: Yes
- Waterproof: Yes

#### **Light characteristics**

· Color rendering index (CRI): 80

#### Miscellaneous

- Especially designed for: Garden & Patio
- Style: Expressive
- Type: Wall Lights
- EyeComfort: Yes

#### Service

Warranty: 1 year(s)

#### **Technical specifications**

- · Total lumen output fixture: 670
- · Bulb technology: LED
- Light color: 3000K
- Mains power: 220-240 V
- · Wattage bulb included: 10
- IP code: IP65 | Dust-tight and jet-
- Class of protection: Class II Double Insulated

#### Packaging dimensions and weight

- EAN/UPC product: 8718696763049
- · Net weight: 0.8 kg
- · Gross weight: 0.85 kg
- · Height: 7.5 cm
- · Length: 17.5 cm
- Width: 11 cm



Issue date: 2025-11-01 Version: 0.437 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips