

## Wall light

Led indoor

12 W

Aluminium

bronze

220-240 V

919215850796



## Light & Relaxed

Flexible neck for adjusting beam. Modern finish for urban homes.  
Long life LED light source

### Easy installation

- Easy installation

### Light effect

- Provides a bright white light

### Sustainable light solutions

- High quality LED light

### Beacon of trust


- You can trust what the Philips packaging is saying

### Premium quality

- Die-casted aluminum for a premium look and feel

# Highlights

## Easy installation



No more hassle in installation. Just fix or hang securely on the wall and plug in, now this luminaire is ready to light on.

## Superior light quality High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

## Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

## Premium materials



# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Bronze
- Material: Aluminium

## Durability

- Nominal lifetime: 25,000

## Extra feature/accessory incl.

- Diffused light effect: Yes
- LED integrated: Yes
- Premium quality material: Yes

## Light characteristics

- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Home office & Study
- Style: Heritage
- Type: Ceiling Lights
- EyeComfort: Yes

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 420
- Bulb technology: LED
- Mains power: 220–240 V
- Energy class included light source: Built in LED
- Wattage bulb included: 12W
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated

## Packaging dimensions and weight

- EAN/UPC - product: 8718696772195
- Net weight: 0.48 kg
- Gross weight: 0.66 kg
- Height: 9.6 cm
- Length: 50.8 cm
- Width: 17.8 cm

919215850796



Issue date: 2026-01-31  
Version: 0.441

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)