

PHILIPS

IP44 Ceiling Light

myBathroom

18W; Warm White; 1650 lumen;
In-built LED;

IP44 rating ensures protection
from dust and moisture;

Attractive golden ring on the
edge;

Perfect for balconies and
bathrooms

919215851068



Combination of functional utility and decorative appeal

Bring home the sleek yet elegant ceiling light with a minimalist design to transform your home space. These lights create a delectable ambience ensuring eye comfort

Wellbeing in your bathroom with high quality light

- Seeing well is essential in the bathroom

Highlights

Seeing well is essential

Seeing well is essential for good results at the mirror, that's why each lamp

features a high quality light source for confident grooming. The bathroom lighting range uses the latest energy

saving technology for good quality light that provides plenty of illumination without being harsh.

Specifications

Bulb characteristics

- Intended use: Indoor

Bulb dimensions

- Height: 6.5 cm

Design and finishing

- Color: White with yellow ring on the edge
- Material: Polycarbonate

Extra feature/accessory incl.

- 4 light recipes: No
- 5 years warranty on the LED module: No
- Adjustable height: No
- Adjustable spot head: No
- Batteries included: No
- Bi-directional light beams: No
- Candle light effect: No
- Centerpiece: No
- Choose your color: No
- Clamp included: Yes
- Color changing (LED): No
- Day-and-night sensor: No
- Defined light beams: No
- Fully weatherproof: No
- Hue bridge included: No
- Hue Switch: No
- Hue Switch Included: No
- LED integrated: Yes
- Perfectly suited for ambiance creation: Yes
- Premium quality material: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bathroom, Balcony
- Style: Contemporary

Product dimensions and weight

- Net weight: 0.406 kg
- Height: 6.5 cm
- Length: 25 cm
- Width: 25 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lamp lifetime up to: 20,000
- Lumen output bulb included: 1,650
- Diameter: 250 mm
- Total lumen output fixture: 1650
- Bulb technology: LED
- Light color: Warm white light
- Mains power: 220-240 V
- Energy class included light source: built in LED + bulb of class A+
- IP code: IP44

Packaging dimensions and weight

- EAN/UPC - product: 8720169166790
- Net weight: 0.41 kg
- Gross weight: 0.58 kg
- Height: 25.2 cm
- Length: 25.2 cm
- Width: 6.9 cm



Issue date: 2026-07-04
Version: 0.159

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com