

919215851093



Bring your outdoors alive!

With modern, minimalistic design, this wall light exudes a distinct look when installed on the walls of buildings, gardens and along pathways. It can be strategically put to highlight your surroundings with exquisite patterns

Designed for outdoors

• IP65 weatherproof rated

Highlights

IP65 weatherproof rated

An IP rating contains two digits which refer to protection against solids, such

as dust, or liquids, such as rain. IP65 means that these light fixtures are protected against water splashed from any direction and are suitable for outdoor use.

Specifications

Bulb characteristics

· Intended use: Outdoor

Bulb dimensions

· Height: 4.3 cm

Design and finishing

· Color: Black

· Material: Aluminium

Extra feature/accessory incl.

· 4 light recipes: No

• 5 years warranty on the LED module: No

· Adjustable height: No

· Adjustable spot head: No

· Batteries included: No

Bi-directional light beams: Yes

· Candle light effect: No

· Centerpiece: No

· Choose your color: No

· Clamp included: Yes

· Color changing (LED): No

· Day-and-night sensor: No

· Defined light beams: No

Fully weatherproof: Yes

· Hue bridge included: No

· Hue Switch: No

· Hue Switch Included: No

· LED integrated: Yes

Perfectly suited for ambiance

creation: Yes

· Premium quality material: Yes

· Waterproof: Yes

Light characteristics

· Color rendering index (CRI): 80

Miscellaneous

• Especially designed for: Garden &

Patio

• Style: Contemporary

Product dimensions and weight

· Net weight: 0.248 kg

· Height: 4.3 cm

· Length: 7.8 cm

· Width: 8.7 cm

Service

· Warranty: 1 year(s)

Technical specifications

Lamp lifetime up to: 20,000

· Lumen output bulb included: 475

• Total lumen output fixture: 475

· Bulb technology: LED

· Light color: warm white

· Mains power: 220-240 V

• Energy class included light source: built in LED + bulb of class A+

• IP code: IP65 | Dust-tight and jet-

proof

Packaging dimensions and weight

• EAN/UPC - product: 8720169176508

· Net weight: 0.25 kg

· Gross weight: 0.27 kg

· Height: 8.6 cm

· Length: 9 cm

· Width: 5 cm



Issue date: 2025-11-01 Version: 0.118 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips