



Set your desired ambiance at your fingertips

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

Designed for your living- and bedroom

- Perfect to relax and socialise
- · Create a stylish and welcoming atmosphere

Ambient light effect

- · Ambience light mode
- Color changing mood light

Light effect

· Cozy light effect

Premium quality

· Premium aesthetic elegant chrome finish

Highlights

Perfect to relax and socialise

The living room is the heart of any home – a place where families gather to relax and guests socialise. Lighting for your living– and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your d?cor and define the localised ambiance you have always desired.

Ambience light mode

Create a cozy, intimate atmosphere with the ambience light mode.

Color changing mood light

The light shifts between different color temperatures to suit your mood

Cozy light effect

Create a warm, comforting environment to wind down and relax in.

Premium aesthetic elegant chrome finish

The elegant chrome finish on this item adds a touch of timeless sophistication to any space.

Specifications

Design and finishing

Color: WhiteMaterial: PVC

Durability

• Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

- · Color rendering index (CRI): 80
- · Color temperature: 3000-6500 K

Miscellaneous

· EyeComfort: Yes

Product dimensions and weight

Net weight: 0.4 kgOverall height: 40 mmOverall length: 1,220 mmOverall width: 30 mm

Service

· Warranty: 1 year(s)

Technical specifications

• Total lumen output fixture: 2000

Light color: 3000-6500
Mains power: 220-241
Wattage bulb included: 20
IP code: IP20 | Finger-protected
Class of protection: Class II - Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8718696908624

Net weight: 0.4 kgGross weight: 0.55 kgHeight: 4 cm

Length: 125 cmWidth: 6 cm



Issue date: 2025-11-15 Version: 0.267 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips