

# PHILIPS

Ceiling light

myLiving

TwinGlow

White



919515813971



## Set your desired ambiance at your fingertips

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

### **Designed for your living- and bedroom**

- Perfect to relax and socialise
- Create a stylish and welcoming atmosphere

### **Ambient light effect**

- Ambience light mode
- Color changing mood light

### **Light effect**

- Cozy light effect

### **Premium quality**

- Premium aesthetic elegant chrome finish

# Highlights

## Perfect to relax and socialise

The living room is the heart of any home - a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

## Create a stylish atmosphere



This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define the localised ambiance you have always desired.

## Ambience light mode

Create a cozy, intimate atmosphere with the ambience light mode.

## Color changing mood light

The light shifts between different color temperatures to suit your mood

## Cozy light effect

Create a warm, comforting environment to wind down and relax in.

## Premium aesthetic elegant chrome finish

The elegant chrome finish on this item adds a touch of timeless sophistication to any space.

# Specifications

## Design and finishing

- Color: White
- Material: PVC

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K

## Miscellaneous

- EyeComfort: Yes

**Product dimensions and weight**

- Net weight: 0.4 kg
- Overall height: 40 mm
- Overall length: 1,220 mm
- Overall width: 30 mm

**Service**

- Warranty: 1 year(s)

**Technical specifications**

- Total lumen output fixture: 2000
- Bulb technology: LED
- Light color: 3000
- Mains power: 220-244
- Wattage bulb included: 20
- IP code: IP20
- Class of protection: Class II - Double Insulated

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions and weight**

- Net weight: 0.4 kg
- Gross weight: 0.55 kg
- Height: 4 cm
- Length: 125 cm
- Width: 6 cm



Issue date: 2026-04-29  
Version: 0.267

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)