



1 x PLC 6.5W 2700K 9290042554

1 x 750 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.36	0.34	0.33	0.33	0.32	0.24	0.22	0.17	0.19	0.15	0.11	0.36	0.34	0.33	0.33	0.32
0.80	0.45	0.42	0.42	0.41	0.40	0.32	0.28	0.23	0.25	0.20	0.15	0.45	0.42	0.42	0.41	0.40
1.00	0.53	0.49	0.49	0.48	0.46	0.38	0.34	0.28	0.30	0.25	0.19	0.53	0.49	0.49	0.48	0.46
1.25	0.60	0.55	0.56	0.54	0.52	0.44	0.39	0.34	0.35	0.30	0.23	0.60	0.55	0.56	0.54	0.52
1.50	0.66	0.60	0.62	0.59	0.57	0.49	0.44	0.39	0.39	0.34	0.27	0.66	0.60	0.62	0.59	0.57
2.00	0.76	0.68	0.71	0.67	0.64	0.57	0.51	0.46	0.45	0.41	0.33	0.76	0.68	0.71	0.67	0.64
2.50	0.82	0.73	0.77	0.73	0.69	0.62	0.56	0.51	0.50	0.46	0.37	0.82	0.73	0.77	0.73	0.69
3.00	0.87	0.76	0.81	0.76	0.72	0.66	0.60	0.55	0.53	0.50	0.40	0.87	0.76	0.81	0.76	0.72
4.00	0.94	0.81	0.87	0.82	0.77	0.72	0.65	0.61	0.58	0.55	0.44	0.94	0.81	0.87	0.82	0.77
5.00	0.98	0.84	0.91	0.85	0.80	0.76	0.68	0.65	0.61	0.58	0.47	0.98	0.84	0.91	0.85	0.80

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	43669	39103	36692	35936	36692	39103	43669
50.0	43407	38531	35990	35198	35990	38531	43407
55.0	43134	37957	35294	34469	35294	37957	43134
60.0	42856	37379	34600	33744	34600	37379	42856
65.0	42573	36796	33903	33018	33903	36796	42573
70.0	42296	36208	33204	32290	33204	36208	42296
75.0	41987	35579	32464	31523	32464	35579	41987
80.0	41780	35014	31779	30808	31779	35014	41780
85.0	41750	34564	31189	30184	31189	34564	41750
90.0	42082	34360	30806	29757	30806	34360	42082

(cd/m²)

Light output ratio 1.00
 Service upward 0.33
 Service downward 0.67

CIE flux code 26 54 79 67 100

UGRcen (4Hx8H, 0.25H) 30

2024-11-22