



I x 92900I9415

I x 400 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.48
Service downward 0.52

CIE flux code 16 41 70 52 100

UGR_{cen} (4Hx8H, 0.25H) 22

Utilisation factor table

Index k	Reflectances (%) for ceiling, walls and working plane (CIE) Room															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.00	0.80	0.80	0.70	0.70
0.60	0.32	0.31	0.30	0.29	0.28	0.21	0.17	0.13	0.14	0.10	0.05	0.00	0.32	0.31	0.30	0.29
0.80	0.41	0.39	0.38	0.37	0.36	0.28	0.23	0.18	0.18	0.14	0.08	0.00	0.41	0.39	0.38	0.37
1.00	0.49	0.45	0.44	0.43	0.41	0.33	0.28	0.23	0.22	0.18	0.10	0.00	0.49	0.45	0.44	0.43
1.25	0.56	0.51	0.51	0.49	0.47	0.39	0.33	0.27	0.26	0.22	0.13	0.00	0.56	0.51	0.51	0.49
1.50	0.62	0.56	0.56	0.54	0.52	0.44	0.37	0.32	0.30	0.26	0.16	0.00	0.62	0.56	0.56	0.54
2.00	0.71	0.63	0.64	0.61	0.58	0.51	0.43	0.38	0.35	0.31	0.20	0.00	0.71	0.63	0.64	0.61
2.50	0.77	0.68	0.70	0.66	0.63	0.56	0.48	0.43	0.39	0.36	0.24	0.00	0.77	0.68	0.70	0.66
3.00	0.82	0.72	0.75	0.70	0.66	0.60	0.51	0.47	0.42	0.39	0.26	0.00	0.82	0.72	0.75	0.70
4.00	0.89	0.77	0.81	0.76	0.71	0.66	0.56	0.52	0.47	0.44	0.30	0.00	0.89	0.77	0.81	0.76
5.00	0.93	0.80	0.85	0.79	0.74	0.70	0.59	0.56	0.50	0.47	0.33	0.00	0.93	0.80	0.85	0.79

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	4389	3838	3557	3471	3557	3838	4389
50.0	4550	3949	3646	3553	3646	3949	4550
55.0	4806	4139	3808	3706	3808	4139	4806
60.0	5029	4300	3941	3832	3941	4300	5029
65.0	5238	4447	4062	3945	4062	4447	5238
70.0	5412	4562	4152	4029	4152	4562	5412
75.0	5607	4692	4255	4124	4255	4692	5607
80.0	5827	4838	4372	4233	4372	4838	5827
85.0	6151	5066	4560	4410	4560	5066	6151
90.0	6549	5347	4794	4631	4794	5347	6549

(cd/m²)

242257-01-

2018-09-21